

LIST OF TABLES

TABLE		PAGE
1.1	Summary of properties and applications of diamond-like carbon thin films	3
2.1	The hybridization of carbon atom	7
2.2	Comparison of major properties of amorphous carbons with those reference materials diamond, graphite, C60 and polyethylene	8
2.3	Summary of acid etch corrosion test	23
3.1	Thermal heating condition of ta-DLC films for each film characterizations	38
4.1	Raman parameters of the as-deposited ta-DLC and the annealed films at different temperatures and times	44
4.2	Area fraction of all fitted peaks under C1s peak of ta-DLC as-deposited and after annealing at 300 °C for 60 min	49
4.3	Area fraction of all fitted peaks under Si2p peak of ta-DLC as-deposited and after annealing at 300 °C for 60 min	51
4.4	Surface roughness of as-deposited ta-DLC films and after annealing at different temperature for 60 min measured by AFM	55
4.5	Surface roughness of as-deposited ta-DLC films and after annealing at different temperature for 60 min measured by XRR	57